

Eaton Freedom NEMA motor control starter

ECN0711CHA-A29R63/C

UPC:786685452081

Dimensions:

- **Height:** 9.2 IN
- **Length:** 16.2 IN
- **Width:** 15.3 IN

Weight:23.5 LB

Warranties:

- 1 year

Specifications:

- **Enclosure:** NEMA 1
- **Type:** Non-combination non-reversing starter
- **Accessories:** With control power transformer
- **Size:** NEMA size 1
- **Actuator:** HAND/OFF/AUTO selector switch
- **Auxiliary Contact:** Side-mounted
- **Contact Configuration:** 1NO-1NC
- **Overload Relay:** 4-20A solid-state relay without ground fault
- **Phase:** Three-phase
- **System Voltage:** 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN0711CHA-A29R63/C](#)

Certifications:

- UL Listed file E1491
- Contact Manufacturer

Product compliance: No Data



