

## Eaton Freedom NEMA motor control starter

ECN0711CPA-A29

UPC:782114314289

### Dimensions:

- **Height:** 9 IN
- **Length:** 16 IN
- **Width:** 15 IN

**Weight:**12.5 LB

### Warranties:

- 1 year

### Specifications:

- **Enclosure:** NEMA 1
- **Type:** Non-combination non-reversing starter
- **Accessories:** Red RUN pilot light with control power transformer
- **Size:** NEMA size 1
- **Auxiliary Contact:** Side-mounted
- **Contact Configuration:** 1NO-1NC
- **Phase:** Three-phase
- **System Voltage:** 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN0711CPA-A29](#)

### Certifications:

- UL Listed file E1491
- Contact Manufacturer

**Product compliance:** No Data

