

## Eaton Freedom NEMA motor control starter

ECN0711EHA-R63/D

UPC:786685452142

### Dimensions:

- **Height:** 12.6 IN
- **Length:** 7.62 IN
- **Width:** 6 IN

**Weight:**23.5 LB

### Warranties:

- 1 year

### Specifications:

- **Enclosure:** NEMA 1
- **Type:** Non-combination non-reversing starter
- **Accessories:** With control power transformer
- **Size:** NEMA size 1
- **Actuator:** HAND/OFF/AUTO selector switch
- **Overload Relay:** 9-45A solid-state relay without ground fault
- **Phase:** Three-phase
- **System Voltage:** 208V/60 Hz primary, 120V/60 Hz secondary control power transformer

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN0711EHA-R63/D](#)

### Certifications:

- UL Listed file E1491
- Contact Manufacturer

**Product compliance:** No Data

