

Eaton Freedom NEMA motor control starter

ECN0711EJA-A30

UPC:782114342480

Dimensions:

- **Height:** 9 IN
- **Length:** 16 IN
- **Width:** 15 IN

Weight:16 LB

Warranties:

- 1 year

Specifications:

- **Enclosure:** NEMA 1
- **Type:** Non-combination non-reversing starter
- **Accessories:** With control power transformer
- **Size:** NEMA size 1
- **Actuator:** HAND/OFF/AUTO Sel. switch with red RUN pilot light
- **Auxiliary Contact:** Side-mounted
- **Contact Configuration:** 2NO
- **Phase:** Three-phase
- **System Voltage:** 208V/60 Hz primary, 120V/60 Hz secondary control power transformer

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN0711EJA-A30](#)

Certifications:

- UL Listed file E1491
- Contact Manufacturer

Product compliance: No Data

