

Eaton Freedom NEMA motor control starter

ECN07A8CBA-P67H5/D7

UPC:786685399478

Dimensions:

- **Height:** 11 IN
- **Length:** 31 IN
- **Width:** 12 IN

Weight:53 LB

Warranties:

- 1 year

Specifications:

- **Enclosure:** NEMA 12
- **Type:** Non-combination non-reversing starter
- **Accessories:** H2007B-3 heater packs with control power transformer
- **Size:** NEMA size 00
- **Actuator:** START/STOP pushbuttons with green RUN light
- **Phase:** Three-phase
- **System Voltage:** 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN07A8CBA-P67H5/D7](#)

Certifications:

- UL Listed file E1491
- Contact Manufacturer

Product compliance: No Data



