



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Line Enclosed Control

ECN1801CJC-A29H5/D8

UPC:786685399737

Dimensions:

- **Height:** 11 IN
- **Length:** 31 IN
- **Width:** 12 IN

Weight:41 LB

Warranties:

- 1 year

Specifications:

- **Enclosure:** NEMA 1
- **Type:** Combination non-reversing starter
- **Accessories:** H2008B-3 heater packs with control power transformer
- **Actuator:** HAND/OFF/AUTO Sel. switch with red RUN pilot light
- **Auxiliary Contact:** Side-mounted
- **Contact Configuration:** 1NO-1NC
- **Fuse Clip Rating:** 30A/600V
- **Fuse Clip Type:** Type R
- **Phase:** Three-phase
- **Size:** NEMA size 0
- **System Voltage:** 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN1801CJC-A29H5/D8](#)

Certifications:

- UL Listed file E1491



Product compliance: No Data

© 2016 Eaton. All rights reserved.