



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Line Enclosed Control

ECN1831CJG-A27P34

UPC:782114201411

Dimensions:

- **Height:** 13 IN
- **Length:** 34 IN
- **Width:** 22 IN

Warranties:

- 1 year

Specifications:

- **Enclosure:** NEMA 1
- **Type:** Combination non-reversing starter
- **Accessories:** Phase monitoring relay with control power transformer
- **Actuator:** HAND/OFF/AUTO Sel. switch with red RUN pilot light
- **Contact Configuration:** 1NO
- **Fuse Clip Rating:** 100A/600V
- **Fuse Clip Type:** Type R
- **Phase:** Three-phase
- **Size:** NEMA size 3
- **System Voltage:** 460V/60 Hz-440V/50 Hz primary, 120/60-110/50 secondary control power transformer

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN1831CJG-A27P34](#)

Certifications:

- UL Listed file E1491

Product compliance: No Data



