



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Line Enclosed Control

ECN2211AHC-A15S29

UPC:782114318256

Dimensions:

- **Height:** 11 IN
- **Length:** 31 IN
- **Width:** 12 IN

Weight:38 LB

Warranties:

- 1 year

Specifications:

- **Coil Voltage:** 110V/50 Hz-120V/60 Hz
- **Enclosure:** NEMA 1
- **Type:** Combination non-reversing starter
- **Actuator:** HAND/OFF/AUTO selector switch
- **Auxiliary Contact:** Top-mounted
- **Contact Configuration:** 1NO-1NC
- **Fuse Clip Rating:** 30A/600V
- **Fuse Clip Type:** Type R
- **Phase:** Single-phase install jumper
- **Size:** NEMA size 1

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN2211AHC-A15S29](#)

Certifications:

- UL Listed file E1491

Product compliance: No Data

