



Powering Business Worldwide

pe.eaton.com

NEMA Freedom Line Enclosed Control

ECN2411EHC-A23P1

UPC:782114318454

Dimensions:

- **Height:** 11 IN
- **Length:** 31 IN
- **Width:** 12 IN

Weight:38 LB

Warranties:

- 1 year

Specifications:

- **Enclosure:** NEMA 1
- **Type:** Combination non-reversing starter—circuit breaker
- **Accessories:** Push-to-test pilot light (red run) wired to coil with control power transformer
- **Actuator:** HAND/OFF/AUTO selector switch
- **Auxiliary Contact:** Top-mounted
- **Circuit Breaker Rating:** 7A
- **Contact Configuration:** 2NO-2NC
- **Phase:** Three-phase
- **Size:** NEMA size 1
- **System Voltage:** 208V/60 Hz primary, 120V/60 Hz secondary control power transformer

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN2411EHC-A23P1](#)

Certifications:

- UL Listed file E1491

Product compliance: No Data



