

## Freedom Industrial Pump Panel

**ECN5552BAJ-P6R63/G**

**UPC:**786685456379

**Dimensions:**

- **Height:** 12 IN
- **Length:** 62 IN
- **Width:** 150 IN

**Weight:**30 LB

**Notes:**NEMA Size 5 starter available with 60–300A panel mounted CTs. Starter as an assembled unit with 1–5A C440 overload relay (C440A1A005SELAX or C440A2A005SELAX).

**Warranties:**

- 1 year

**Specifications:**

- **Coil Voltage:** 220V/50 Hz-240V/60 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Type:** Circuit breaker disconnect
- **Circuit Breaker Rating:** 250A
- **Overload Relay:** 60-300A solid-state relay without ground fault
- **Size:** NEMA size 5
- **Special Features:** Pushbutton omitted

**Supporting documents:**

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN5552BAJ-P6R63/G](#)

**Certifications:**

- OSHPD Certified
- UL Listed
- cUL Listed

**Product compliance:** No Data

