



Powering Business Worldwide

pe.eaton.com

XT IEC Line Non-Metallic Enclosed Control

ECX09F5AAA-R63/D

UPC:786685556017

Dimensions:

- **Height:** 13.31 IN
- **Length:** 6.7 IN
- **Width:** 9.84 IN

Weight:10 LB

Notes:Non-Combination Ampere Rating. See Tab 1 for enclosure type/IP rating cross-reference. No disconnect.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 120V
- **Enclosure:** IP66, NEMA 4X-watertight (non-metallic)
- **Amperage Rating:** 18A
- **Class:** Non-combination
- **Full Load Current Range:** 9-45 FLA
- **Operation:** Non-reversing

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [ECX Non-metallic Starters To 25 HP](#)
- [Eaton Specification Sheet - ECX09F5AAA-R63/D](#)

Certifications:

- CSA Certified
- UL Listed
- IEC Rated



Product compliance: No Data

© 2016 Eaton. All rights reserved.