



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## XT IEC Line Non-Metallic Enclosed Control

ECX09F5ABA-R63/D

UPC:786685556109

### Dimensions:

- **Height:** 13.31 IN
- **Length:** 6.7 IN
- **Width:** 9.84 IN

**Weight:** 10 LB

**Notes:** Non-Combination Ampere Rating. See Tab 1 for enclosure type/IP rating cross-reference. No disconnect.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Voltage:** 120V
- **Enclosure:** IP66, NEMA 4X-watertight (non-metallic)
- **Amperage Rating:** 18A
- **Actuator:** START/STOP pushbuttons
- **Class:** Non-combination
- **Full Load Current Range:** 9-45 FLA
- **Operation:** Non-reversing

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [ECX Non-metallic Starters To 25 HP](#)
- [Eaton Specification Sheet - ECX09F5ABA-R63/D](#)

### Certifications:

- UL Listed
- CSA Certified



- IEC Rated

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.