



Powering Business Worldwide

pe.eaton.com

Definite Purpose Molded Case Circuit Breaker

FPS3080W

UPC:786685554075

Dimensions:

- **Height:** 6 IN
- **Length:** 3.38 IN
- **Width:** 4.13 IN

Weight:5 LB

Notes:FP (15-225A), KP (200-400A), LP (450-600A) and MP (700-800A) Frames ship standard without lugs or mounting hardware, offering additional flexibility

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 80A
- **Interrupt Rating:** 65 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600V
- **Frame Size:** FP-frame
- **Terminals:** Without
- **Trip Type:** Thermal-magnetic

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - FPS3080W](#)

Certifications:

- UL 489

Product compliance: No Data



