



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Molded Case Engine Generator Circuit Breaker

**JG3125CT**

**UPC:**786679108840

### Dimensions:

- **Height:** 6 IN
- **Length:** 12 IN
- **Width:** 7 IN

**Weight:**9.21 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 125A
- **Number Of Poles:** Three-pole
- **Accessories:** Center tap studs for dual voltage applications
- **Feed Type:** Reverse
- **Frame:** JG-frame
- **Series:** Series C
- **Terminals:** Line and load
- **Trip Type:** Thermal magnetic

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - JG3125CT](#)

### Certifications:

- CSA Certified
- UL 489
- IEC Rated
- UL Listed
- CSA Std. C22.2 No. 5
- IEC 947-2



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.