



Powering Business Worldwide

pe.eaton.com

NGR Rocker Switch Base

NGR10021BN00N

UPC:786685239705

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

Specifications:

- **Type:** No rocker assembled
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc (14 Vdc rating)
- **Circuit Number:** 1002
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** MOM. ON
- **Contact Material:** Standard plating
- **Frame Color:** Black
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250 in spade
- **Texture:** Matte
- **Throw Type:** Single-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - NGR10021BN00N](#)

Certifications:



- Approvable under stringent UL and CSA standards

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.