



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NGR Rocker Switch Base

NGR1504GBG0GN

UPC:786685617916

### Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

**Weight:**8 LB

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

### Specifications:

- **Type:** No rocker assembled
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 1504
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** ON
- **Contact Material:** Gold plated
- **Frame Color:** Black
- **Lamp Color:** None (top)-green (bottom)
- **Lamp Voltage:** 14V
- **Mounting:** Snap-in mounting
- **Number Of Poles:** Single-pole
- **Style:** Locking (down position)
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Single-throw

### Supporting documents:

- [Eaton's Volume 11-Vehicle and Commercial](#)



## Controls

- [Eaton Specification Sheet - NGR1504GBG0GN](#)

## **Certifications:**

- CSA Certified
- UL Listed

## **Product compliance:**

- RoHS Compliant