



Powering Business Worldwide

pe.eaton.com

New Generation Rockers Switch Base

NGR15282BGYGN

UPC:786685540412

Dimensions:

- **Height:** 1.8 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 1528
- **Circuit Position Center:** NONE
- **Circuit Position Down:** OFF
- **Circuit Position Up:** MOM ON
- **Contact Material:** Gold plated
- **Frame Color:** Black
- **Lamp Color:** Amber-green
- **Lamp Voltage:** 14V
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Style:** Palm guard (top)
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - NGR15282BGYGN](#)



Certifications:

- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.