



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## NGR Rocker Switch Base

**NGR35081BNAAN**

**UPC:**786685682488

### Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

**Weight:**9 LB

### Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warrantied for one (1) year from the date of shipment.

### Specifications:

- **Type:** No rocker assembled
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 3508
- **Circuit Position Center:** ON
- **Contact Material:** Standard plating
- **Frame Color:** Black
- **Lamp Color:** Clear (top)-clear (bottom)
- **Lamp Voltage:** 14 Vdc
- **Mounting:** Snap-in mounting
- **Number Of Poles:** Two-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

### Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - NGR35081BNAAN](#)



**Certifications:**

- CSA Certified
- UL Listed

**Product compliance:**

- RoHS Compliant

---

© 2016 Eaton. All rights reserved.