



Powering Business Worldwide

pe.eaton.com

New Generation Rockers Switch Base

NGR35881BNAAN

UPC:786685015330

Dimensions:

- **Height:** 1.8 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

Notes:Lamp type is replaceable

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 3588
- **Circuit Position Center:** ON
- **Circuit Position Down:** MOM ON
- **Contact Material:** Standard plating
- **Frame Color:** Black
- **Lamp Voltage:** 14 Vdc
- **Mounting:** Snap-in
- **Number Of Poles:** Two-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents: No Data

Certifications:

- UL Listed
- CSA Certified



Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.