



Powering Business Worldwide

pe.eaton.com

New Generation Rockers Switch Base

NGR55043BN0BN

UPC:786685444956

Dimensions:

- **Height:** 1.8 IN
- **Length:** 1.97 IN
- **Width:** 1.024 IN

Notes:Lamp type is replaceable

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 5504
- **Circuit Position Center:** NONE
- **Circuit Position Down:** ON
- **Circuit Position Up:** OFF
- **Contact Material:** Standard plating
- **Frame Color:** Black
- **Lamp Color:** Clear
- **Lamp Voltage:** 24 Vdc incandescent
- **Mounting:** Snap-in
- **Number Of Poles:** Single-pole
- **Style:** Palm guard (bottom)
- **Terminals:** 0.250-inch spade terminal
- **Texture:** Matte
- **Throw Type:** Double-throw

Supporting documents:

- [Eatons Volume 11-Vehicle and Commercial](#)



Controls

- [Eaton Specification Sheet - NGR55043BN0BN](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant