



Powering Business Worldwide

pe.eaton.com

NGR Rocker Switch Base

NGR55061BNECN

UPC:786685673936

Dimensions:

- **Height:** 5 IN
- **Length:** 13 IN
- **Width:** 12 IN

Weight:8 LB

Notes:PCB version LED.

Warranties:

- Eaton Selling Policy 25-000, two (2) years from the date of shipment, excluding incandescent bulbs. LEDs and X Series products are warranted for one (1) year from the date of shipment.

Specifications:

- **Type:** No rocker assembled
- **Amperage Rating:** 15A at 125 Vac, 10A at 250 Vac, 15A at 28 Vdc
- **Circuit Number:** 5506
- **Circuit Position Center:** NONE
- **Circuit Position Down:** ON
- **Circuit Position Up:** OFF
- **Contact Material:** Standard plating
- **Frame Color:** Black
- **Lamp Color:** Amber (top)-red (bottom)
- **Lamp Voltage:** 28V
- **Mounting:** Snap-in mounting
- **Number Of Poles:** Single-pole
- **Style:** Rocker and paddle frame
- **Terminals:** 0.250 in spade terminal
- **Texture:** Matte
- **Throw Type:** Single-throw

Supporting documents:



- [Eatons Volume 11-Vehicle and Commercial Controls](#)
- [Eaton Specification Sheet - NGR55061BNECN](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- RoHS Compliant

© 2016 Eaton. All rights reserved.