



Powering Business Worldwide

pe.eaton.com

Mini-Power Center

P48G11E25CUB

UPC:786680097348

Dimensions:

- **Height:** 43.37 IN
- **Length:** 14.58 IN
- **Width:** 20.41 IN

Weight:375 LB

Notes:All copper construction (coil and interior) and accepts bolt-on branch breakers from the BAB family

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Electrostatically shielded
- **Type:** Mini-power center
- **Coil Material:** Copper windings
- **Enclosure:** NEMA 3R
- **Frame:** 310
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at -5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 25 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 122A25K

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - P48G11E25CUB](#)



Certifications:

- IEEE Certified
- UL Listed
- ANSI
- CSA Certified

Product compliance:

- NEMA Compliant

© 2016 Eaton. All rights reserved.