



Powering Business Worldwide

pe.eaton.com

Mini-Power Center

P48G11S15CUS6

UPC:786680103711

Dimensions:

- **Height:** 37.5 IN
- **Length:** 11.6 IN
- **Width:** 13.1 IN

Weight:322 LB

Notes:Grade 316 stainless steel enclosure (does not imply NEMA 4X rating)

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Mini-power center
- **Coil Material:** Copper windings
- **Enclosure:** NEMA 3R
- **Frame:** 286
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 480V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at -5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 15 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 107A15K

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - P48G11S15CUS6](#)

Certifications:

- UL Listed



- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.