



Powering Business Worldwide

pe.eaton.com

Hydraulic Magnetic Supplementary Protector

SPHM1RM02R5A

UPC:786685411200

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:One A or B contact maximum per pole.
Contacts rated 10A at 250V arranged left to right.

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 2.5A
- **Number Of Poles:** Single-pole
- **Frequency Rating:** 50-60 Hz
- **Auxiliary Switch:** Normally open auxiliary switch
- **Enclosure:** IP20
- **Inrush Delay:** 18 X
- **Time Delay:** Medium

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - SPHM1RM02R5A](#)

Certifications:

- IEC 60947-2
- CSA Certified
- UL Listed

Product compliance:

- DIN VDE 0600

