



Powering Business Worldwide

pe.eaton.com

Hydraulic Magnetic Supplementary Protector

SPHM2YL0030

UPC:786679757024

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Maximum of 40A at 25X inrush.

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 30A
- **Number Of Poles:** Two-pole
- **Frequency Rating:** 50-60 Hz
- **Enclosure:** IP20
- **Inrush Delay:** 25 X
- **Time Delay:** Long

Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - SPHM2YL0030](#)

Certifications:

- UL Listed
- IEC 60947-2
- CSA Certified

Product compliance:

- DIN VDE 0600

