



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Hydraulic Magnetic Supplementary Protector

**SPHM2YL02R5**

**UPC:**786679756881

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**Maximum of 40A at 25X inrush.

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 2.5A
- **Number Of Poles:** Two-pole
- **Frequency Rating:** 50-60 Hz
- **Enclosure:** IP20
- **Inrush Delay:** 25 X
- **Time Delay:** Long

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - SPHM2YL02R5](#)

### Certifications:

- CSA Certified
- IEC 60947-2
- UL Listed

### Product compliance:

- DIN VDE 0600

