



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Hydraulic Magnetic Supplementary Protector

**SPHM3HS0025A**

**UPC:**782116125333

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**One A or B contact maximum per pole.  
Contacts rated 10A at 250V arranged left to right.

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 25A
- **Number Of Poles:** Three-pole
- **Frequency Rating:** 50-60 Hz
- **Auxiliary Switch:** Normally open auxiliary switch
- **Enclosure:** IP20
- **Inrush Delay:** 8 X
- **Time Delay:** Short

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - SPHM3HS0025A](#)

### Certifications:

- UL Listed
- CSA Certified
- IEC 60947-2

### Product compliance:

- DIN VDE 0600

