



Powering Business Worldwide

pe.eaton.com

Hydraulic Magnetic Supplementary Protector

SPHM3YL0025

UPC:786679757307

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Maximum of 40A at 25X inrush.

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 25A
- **Number Of Poles:** Three-pole
- **Frequency Rating:** 50-60 Hz
- **Enclosure:** IP20
- **Inrush Delay:** 25 X
- **Time Delay:** Long

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - SPHM3YL0025](#)

Certifications:

- UL Listed
- CSA Certified
- IEC 60947-2

Product compliance:

- DIN VDE 0600

