



Powering Business Worldwide

pe.eaton.com

XT IEC FVR Starter

XTAR040D11C040

UPC:782116886531

Dimensions:

- Height: X
- Length: X
- Width: X

Notes: Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 40A
- **Auxiliary Contact:** Side-mounted
- **Coil:** 415V 50 Hz, 480V 60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Overload Range:** 24-40A
- **Terminals:** Screw terminals

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTAR040D11C040](#)

Certifications:

- EN 60947
- CSA Certified
- IEC 60947
- UL Listed

Product compliance:

- RoHS Compliant
- ATEX Compliant
- CE Marked



