



Powering Business Worldwide

pe.eaton.com

XT IEC FVR Starter

XTAR040D11H5G100

UPC:786685459554

Dimensions:

- Height: 1 IN
- Length: 1 IN
- Width: 1 IN

Weight:1 LB

Notes: Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- Amperage Rating: 40A
- Auxiliary Contact: Side-mounted
- Coil: 240V 50 Hz, 277V 60 Hz
- Contact Configuration: 1NO-1NC
- Frame Size: 55 mm
- Overload Range: 20-100A
- Terminals: Screw terminals

Supporting documents:

- [Eaton's Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTAR040D11H5G100](#)

Certifications:

- UL Listed
- EN 60947
- CSA Certified
- IEC 60947

Product compliance:

- CE Marked
- ATEX Compliant
- RoHS Compliant



