



Powering Business Worldwide

pe.eaton.com

XT IEC FVR Starter

XTAR040D11R3E045

UPC:786685092973

Dimensions:

- **Height:** 9.75 IN
- **Length:** 8 IN
- **Width:** 8 IN

Weight:4.7 LB

Notes:Screw terminals (6-65A); 5 mm (80-150A);
no lugs (185-2000A)

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 40A
- **Auxiliary Contact:** Side-mounted
- **Coil:** 12V 50/60 Hz
- **Contact Configuration:** 1NO-1NC
- **Frame Size:** 55 mm
- **Overload Range:** 9-45A
- **Terminals:** Screw terminals

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - XTAR040D11R3E045](#)

Certifications:

- IEC 60947
- UL Listed
- CSA Certified
- EN 60947

Product compliance:

- ATEX Compliant
- RoHS Compliant
- CE Marked



