

**PRODUCT:** | **E2500**

**PURPOSE:** | **CLINICAL ROTATOR**

Eberbach's Clinical Rotator E2500 is designed for V.D.R.L., Mazzini, Kline, Boerner-Jones-Luken, cardiolipin, other serological tests, and clinical applications within a speed range of 30 - 220 rpm. A 13" square platform with sponge rubber pad orbits 6" above the bench. The new controller has a digital tachometer along with digital countdown timer. The programmable timer can be selected for timed operation or the unit can be switched for constant operation. The 30W motor has permanently lubricated bearings and is rated for continuous operation in the load range of up to 12 lbs. The Case measures 13" x 14" and is mounted on four suction feet to reduce creeping. At a given speed setting the motor maintains a constant speed regardless of changes in line voltage, load or temperature variations. Every point on the surface of the rotator travels through a uniform .75" diameter circle in the horizontal plane.



### PRODUCT SPECIFICATIONS...

<b>ROTATING SPEED:</b>	30 - 220 rpm
<b>TYPE OF MOUNTING:</b>	<ul style="list-style-type: none"> <li>• Bench top</li> <li>• Suction cup feet to prevent creeping</li> </ul>
<b>LOAD CAPACITY:</b>	Accepts loads up to 12 lbs
<b>POWER REQUIREMENTS:</b>	115V/230V, 50/60Hz
<b>POWER CONSUMPTION:</b>	30 Watts
<b>SIZE AND WEIGHT:</b>	Length: 14.3", Width: 13.2", Height: 5.2" Weight: 20 lbs
<b>OPTIONS:</b>	<ul style="list-style-type: none"> <li>• Slide Carrier (Order No. E2550) holds nine 50 x 75 mm slides; aluminum carrier is formed to fit over the 13" square platform of the Rotator</li> <li>• Slide Carrier (Order No. E2560) similar to No. E2550 Carrier but designed to hold nine 58 x 75 mm slide</li> <li>• Plastic Cover (Order No. E2565) for covering the platform of the Model E2500 Clinical Rotator, or No. E2550 - E2560 Slide Carriers</li> <li>• Incubator Compatible Model Available. Call for Details.</li> </ul>

**DURABILITY • CRAFTSMANSHIP • QUALITY**