

# Beacons

## Rotating Incandescent

### 100SB Series

Edwards 100SB Series rotating beacons are heavy duty visual signals designed with dual sealed beam lamps that rotate 360 degrees within a high impact polycarbonate dome. The PVC coated base allows for greater corrosion resistance and durability. Features a quiet belt drive for simplified maintenance.

#### Features and Specifications

- Incandescent light source
- Dual sealed beams
- PVC coated base
- Quiet belt drive for simplified maintenance
- 3/4" NPT conduit mounting
- NEMA Type 3R enclosure
- For outdoor applications, lens should face up



#### Ordering Information

Description	Cat. No.	Operating Voltage <sup>1</sup>	Current	Dome Colors	Flash Rate	Peak Candela	Replacement		
							Dome	Belt	Lamp
Rotating Light Incandescent	100SBA-N5	120V AC	0.8 A	Amber	80 fpm	35,000	100SB-LA		
	100SBB-N5	120V AC	0.8 A	Blue	80 fpm	35,000	100SB-LB		
	100SBC-N5	120V AC	0.8 A	Clear	80 fpm	35,000	100SB-LC	100SB-RB	GE #4416-1
	100SBG-N5	120V AC	0.8 A	Green	80 fpm	35,000	100SB-LG		900 hours. <sup>2,3</sup>
	100SBR-N5	120V AC	0.8 A	Red	80 fpm	35,000	100SB-LR		

<sup>1</sup>AC voltage frequency is 50/60 Hz

<sup>2</sup>Projected life based on manufacturer's calculated lamp life.

<sup>3</sup>User supplied

#### Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
100SBA-N5	7.72	8.64
100SBB-N5	7.72	8.64
100SBC-N5	7.72	8.64
100SBG-N5	7.72	8.64
100SBR-N5	7.72	8.64

