

StackLight™ 101 Series

Edwards 101 Series StackLight is a versatile signaling device that may contain up to five light modules and a pulsating horn in a single, integrated stack. The 85dB pulsating horn can be operated as a sixth independent signal or in conjunction with any one of the five light modules available.

The lens modules are available with LED, Incandescent or Strobe light sources. Options for steady-on, flashing or multi-mode are available. Ideal for heavy-duty use in locations where visibility over longer distances is required.

Features and Specifications

- LED, Incandescent, Halogen and Strobe light source
- Steady-on, flashing or multi-mode (flashing or steady-on)
- Base unit includes a pulsating horn, 95dB at 1 meter/85dB at 10 feet
- Option for panel or conduit mounting
- Can be mounted for use in indoor or outdoor applications (lens facing up for outdoor use).
- Designed for 4" octagonal box mounting



Ordering Information

Description	Cat. No.	Operating Voltage ¹	Current	Lens/ LED Colors	Lamp Life	Flash Rate	Replacement Horns	Replacement Lamps
Base Unit with Horn	101BS-N5	120V AC	0.05 A	—	—	—	123A-N5	—
	101BS-E1	12V DC	0.05 A	—	—	—	P-047570-0743	—
	101BS-G1	24V DC	0.05 A	—	—	—	P-047570-0743	—

Module Type	Cat. No.	Operating Voltage	Current	Lens/ LED Colors	Lamp Life	Flash Rate	Peak Candela	Replacement Lamps
Steady-on Incandescent	101SINR-E1	12V DC	1.0 A	Red	1,520 hours ²	—	2374	Industry trade No. 94 ⁴
	101SING-E1	12V DC	1.0 A	Green	1,520 hours ²	—	2374	
	101SINA-E1	12V DC	1.0 A	Amber	1,520 hours ²	—	2374	
	101SINB-E1	12V DC	1.0 A	Blue	1,520 hours ²	—	2374	
	101SINM-E1	12V DC	1.0 A	Magenta	1,520 hours ²	—	2374	
	101SINC-E1	12V DC	1.0 A	Clear	1,520 hours ²	—	2374	
Steady-on Halogen	101SINHR-G1	24V DC	0.32 A	Red	15,000 hours ²	—	653	50LMP– 9WH-D or industry trade no. 1692 ^{3,4}
	101SINHG-G1	24V DC	0.32 A	Green	15,000 hours ²	—	653	
	101SINHA-G1	24V DC	0.32 A	Amber	15,000 hours ²	—	653	
	101SINHB-G1	24V DC	0.32 A	Blue	15,000 hours ²	—	653	
	101SINH M-G1	24V DC	0.32 A	Magenta	15,000 hours ²	—	653	
	101SINHC-G1	24V DC	0.32 A	Clear	15,000 hours ²	—	653	

¹AC voltage frequency is 50/60 Hz
²Calculated at 65 fpm and 50% duty cycle
³Incandescent lamp
⁴User supplied



StackLight™ 101 Series

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
101BS-N5	1.40	1.74
101BS-E1	1.40	1.74
101BS-G1	1.40	1.74
101SIN*-E1	0.63	0.79
101SINH*-G1	0.63	0.79
101SINH*-N5	0.63	0.79
101FIN*-E1	0.66	0.82
101FINH*-N5	0.66	0.82
101FINH*-G1	0.66	0.82
101ST*-N5	0.72	0.88
101ST*-E1	0.72	0.88
101ST*-G1	0.72	0.88
101XBRM**	0.81	0.97

*Letter in this position designates lens color: A - amber, B - blue, G - green, R - red, C - Clear, or M - magenta

**Letter in this position designates lens/LED color: A - amber, B - blue, G - green, R - red, or W - clear/white

