

# Beacons

## Steady-On LED or Incandescent

### 120 Class



The 120 Class multi-light source beacons are steady-on and require either an LED bulb or 5W incandescent bulb (sold separately).

The lenses are made from a self-extinguishing polycarbonate material, and are offered in amber, blue, green, red and clear.

The 120 Class are UL listed and carry a NEMA Type 4X and IP65 environmental rating.

### Features and Specifications

- LED or Incandescent light source
- Five lens colors
- NEMA Type 4X and IP65 rated enclosure
- Multiple mounting options
- Operating temperature range: -22°F to 122°F (-30°C to 50°C)

### Ordering Information

Description	Cat. No.	Operating Voltage	Current	Lens Colors	Watts	Candela
Steady-on Beacon	120SB12240AD	12-240V AC/DC	0.43 - 0.022 A	Blue	5	4.0 - 2.5
	120SA12240AD	12-240V AC/DC	0.43 - 0.022 A	Amber	5	4.0 - 2.5
	120SR12240AD	12-240V AC/DC	0.43 - 0.022 A	Red	5	4.0 - 2.5
	120SG12240AD	12-240V AC/DC	0.43 - 0.022 A	Green	5	4.0 - 2.5
	120SW12240AD	12-240V AC/DC	0.43 - 0.022 A	Clear	5	4.0 - 2.5

### Accessories

Description	Cat. No.
Junction Box	270JBX
Footing with Extension	270KIT
Threaded Extension Pole 100mm	270TEP
Threaded Footing	270THF
Threaded Wall Mount	270TWM
Double Threaded Wall Mount	270TWM2
Female Adapter Base	270FMLADAPT



VISUAL SIGNALS

# Beacons

## Steady-On LED or Incandescent

### 120 Class

Bulbs			
Description	Cat. No.	Operating Voltage	LED Color
LED Bulb	270LEDB120V	120V AC	Blue
	270LEDA120V	120V AC	Amber
	270LEDR120V	120V AC	Red
	270LEDG120V	120V AC	Green
	270LEDW120V	120V AC	White
	270LEDB240V	230/240V AC	Blue
	270LEDA240V	230/240V AC	Amber
	270LEDR240V	230/240V AC	Red
	270LEDG240V	230/240V AC	Green
	270LEDW240V	230/240V AC	White
	270LEDB12V	12V AC/DC	Blue
	270LEDA12V	12V AC/DC	Amber
	270LEDR12V	12V AC/DC	Red
	270LEDG12V	12V AC/DC	Green
	270LEDW12V	12V AC/DC	White
	270LEDB24V	24V AC/DC	Blue
	270LEDA24V	24V AC/DC	Amber
	270LEDR24V	24V AC/DC	Red
	270LEDG24V	24V AC/DC	Green
	270LEDW24V	24V AC/DC	White
5W Incandescent Bulb	2705W120V	120V AC	
5W Incandescent Bulb-25 Pack	2705W120V25PK	120V AC	
5W Incandescent Bulb	2705W240V	240V AC	
5W Incandescent Bulb-25 Pack	2705W240V25PK	240V AC	
5W Incandescent Bulb	2705W12V	12V AC/DC	
5W Incandescent Bulb-25 Pack	2705W12V25PK	12V AC/DC	
5W Incandescent Bulb	2705W24V	24V AC/DC	
5W Incandescent Bulb-25 Pack	2705W24V25PK	24V AC/DC	
5W Incandescent Bulb	2705W48V	48V AC/DC	
5W Incandescent Bulb-25 Pack	2705W48V25PK	48V AC/DC	



Weights and Dimensions		
Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
120SB12240AD	0.33	0.99
120SA12240AD	0.33	0.99
120SR12240AD	0.33	0.99
120SG12240AD	0.33	0.99
120SW12240AD	0.33	0.99
270JBX	0.22	0.90
270KIT	0.13	1.10
270TEP	0.07	0.22
270THF	0.07	0.29
270TWM	0.09	0.59
270TWM2	0.11	0.62
270FMLADAPT	0.02	0.26

