

Bells Vibrating 55 Series

Edwards 55 Series single magnet vibrating bells feature an exposed striker with an enclosed grounded terminal and case. They are ideal for light duty installations in factory and office environments and OEM applications. They are also suitable for AC powered security systems with a battery standby.

Features and Specifications

- Gray finish
- Low current drain permits long wire runs
- 4" and 6" gong sizes



Ordering Information

Description	Cat. No.	Operating Voltage	Current	VA	Gong Size	dB at 1m/10ft.	DC Coil Res (Ohms)
AC	55-4G5	24V AC	0.20 A	4.8	4" (102mm)	78/68	20.0
	55-6G5	24V AC	0.20 A	4.8	6" (152mm)	84/74	24.0
AC/DC	55-4AM	6V DC	0.85 A	5.1	4" (102mm)	78/68	2.2
		8V AC	1.10 A	8.8			
	55-6AM	6V DC	0.80 A	4.8	6" (152mm)	84/74	1.9
		8V AC	1.00 A	8.0			

Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)	Dimensions		
			A	B	C
55-4AM	0.96	1.08	4" (102mm)	2 1/8" (54mm)	7 3/8" (187mm)
55-4G5	0.96	1.08	4" (102mm)	2 1/8" (54mm)	7 3/8" (187mm)
55-6AM	1.13	2.50	6" (152mm)	2 5/8" (67mm)	10 5/8" (270mm)
55-6G5	1.13	2.50	6" (152mm)	2 5/8" (67mm)	10 5/8" (270mm)

