

# Electronic Audible Signals

## Speaker Amp

### Millennium Class



The 5560M Millennium Mini-Mi™ is a compact tone and voice generator which is completely modular in construction. The 5560M base unit is supplied with or without a 110 candela strobe. The strobe turns on when power is supplied. One of five optional modules may be installed in the base unit.

The 5560M is configured for stand-alone operation when installed with the 556T-M Tone Module Board. One tone may be dipswitch selected from a field of 55 tones and will be played whenever power is applied to the unit. When installed with the 556T-M485 Tone Module Board, any of the available 55 tones can be activated over a RS485 Network.

### Features and Specifications

- Compact, modular design allows unit to be configured with tone, voice, audio coupling or RS485
- 10, 25 or 70.7VRMS audio input boards available
- Internal volume control
- Strobe and diode polarized fire alarm models
- Suitable for outdoor applications when mounted to outdoor back box
- Rugged Lexan construction tone, voice, audio coupling or RS485
- NEMA Type 3R (**Mini-Mi models only**)
- 90dB @ 1m (80dB @ 10ft.)

### Ordering Information

Description	Cat. No.	Operating Voltage <sup>1</sup>	Typical Current (A)		Max. RMS-mA	Color
			Standby	Tone On	Operating Current	
Base Model	5560M-AQ	24V DC	0.03	0.07	—	White
		24V AC	0.08	0.28	—	
Base Model	5560M-N5	120V AC	0.03	0.09	—	White
Diode Polarized	5560MD-FJ	24V DC <sup>3</sup>	—	—	0.13	White
Diode Polarized	5560MDR-FJ	24V DC <sup>3</sup>	—	—	0.13	Red
With Strobe	5560MS-AQ	24V DC	0.03	0.27	—	White
		24V AC	0.08	0.36	—	
With Strobe	5560MS-N5	120V AC	0.03	0.10	—	White
With Strobe - Diode Polarized	5560MDS-FJ	24V DC <sup>3</sup>	—	—	0.13	White
With Strobe - Diode Polarized	5560MDSR-FJ	24V DC <sup>3</sup>	—	—	0.13	Red
Audio Coupler Module Board <sup>2</sup>	556A-M	—	—	—	—	—
Audio Coupler Module Board with RS485 Connectivity <sup>2</sup>	556A-M485	—	—	—	—	—
Tone Module Board <sup>2</sup>	556T-M	—	—	—	—	—
Tone Module Board with RS485 Connectivity <sup>2</sup>	556T-M485	—	—	—	—	—
Voice Module Board <sup>2</sup>	556V-M	—	—	—	—	—

<sup>1</sup>AC voltage frequency is 50/60 Hz.

<sup>2</sup>Not NEMA 3R

<sup>3</sup>Regulated

### Accessories

Description	Cat. No.
Outdoor Back Box	449



# Electronic Audible Signals

## Speaker Amp

### Millennium Class

#### Weights and Dimensions

Cat. No.	Approx. Net Weight (lb.)	Approx. Shipping Weight (lb.)
5560M-AQ	1.50	2.20
5560M-N5	1.50	2.20
5560MD-FJ	1.50	2.20
5560MDR-FJ	1.50	2.20
5560MS-AQ	1.90	2.50
5560MS-N5	2.30	2.70
5560MDS-FJ	1.80	2.30
5560MDSR-FJ	1.80	2.30
556A-M	0.10	0.30
556A-M485	0.10	0.30
556T-M	0.10	0.30
556T-M485	0.10	0.30
556V-M	0.10	0.30
449	1.13	1.18

