

Bells Vibrating 740 and 744

Edwards 740 and 744 bells with an exposed gong are non-adjustable, and are suitable for use in residential, commercial and OEM applications. They may be operated off of a 591 or 592 transformer or DC power. They are also suitable for AC powered security systems with a battery standby.

Features and Specifications

- Exposed gong
- Attractive snap-on covers
- Corrosion resistant chrome finish
- Enclosed binding posts



Ordering Information

| Description | Cat. No. | Operating Voltage | Current | VA | dB at 1m/10ft. | DC Coil Res (Ohms) |
|---------------------------|----------|-------------------|-----------|------|----------------|--------------------|
| Non Adjustable, Vibrating | 740 | 6-8V AC 3-6V DC | 1.0 A max | 7.0 | 100/90 | 1.5 |
| | 744 | 6-8V AC 3-6V DC | 1.0 A max | 10.0 | 100/90 | 1.5 |

Weights and Dimensions

| Cat. No. | Approx. Net Weight (lb.) | Approx. Shipping Weight (lb.) | Dimensions | | |
|----------|--------------------------|-------------------------------|---------------|---------------|----------------|
| | | | A | B | C |
| 740 | 0.40 | 0.42 | 2 1/2" (64mm) | 1 1/4" (32mm) | 5 3/4" (146mm) |
| 744 | 0.52 | 0.58 | 4" (102mm) | 1 3/4" (44mm) | 6 7/8" (175mm) |

