

Transformers

AC - Power

88 Series

Edwards 88 Series Power Transformers provide low voltage source from 50 to 250 volt amps for all large signaling installations.

Holes are provided in transformer housing for surface mounting.

Features and Specifications

- Enclosed connections
- Primary Pigtails
- Screw terminal connections on secondary



Ordering Information		Secondary		
Description	Cat. No.	Primary Voltage ¹	Volts	VA
Power Transformers	88-50	120V AC	24V	50
			12V	25
	88-Y50	240V AC	24V	50
			12V	25
	88-100	120V AC	24V	100
			12V	50
	88-Y100	240V AC	24V	100
			12V	50
	88-250	120V AC	24V	250
			20V	200
16V			160	
12V			125	
			8V	80
			4V	40

¹AC voltage frequency is 50/60 Hz

