

# Conventional and Addressable Accessories

## Relays

### MR Series

The Edwards MR-199 Heavy Duty Power Relays are designed for control applications where 30 Amp DPDT contacts are required. Two models are available; 115V AC coil and 24V DC coil, each of which may be mounted in a rugged steel enclosure.

#### Features and Specifications

- Heavy duty 30 Amp DPDT contacts
- 24V DC or 120V AC models available
- Sturdy metal enclosure
- Operating temperature range: 32°F to 120°F (0°C to 49°C)



#### Ordering Information

Description	Cat. No.	Operating Voltage	Current	Contacts	Contact Rating	Includes Enclosure
Heavy Duty Power Relays	MR199X13	24V DC	0.085 A	DPDT	30 A @ 300V AC	No
	MR199X13/C	24V DC	0.085 A	DPDT	30 A @ 300V AC	Yes
	MR199AX14	120V AC	0.085 A	DPDT	30 A @ 300V AC	No
	MR199AX14/C	120V AC	0.085 A	DPDT	30 A @ 300V AC	Yes

#### Weights and Dimensions

Cat. No.	Approx. Shipping Weight (lb.)	Dimensions		
		Height (in.)	Width (in.)	Depth (in.)
MR199X13	0.8	3.13 (79.4mm)	2.5 (63.5mm)	2.31 (58.7mm)
MR199X13/C	0.9	5.31 (134.9mm)	3.38 (85.9mm)	3.13 (96.8mm)
MR199AX14	0.8	3.13 (79.4mm)	2.5 (63.5mm)	2.31 (58.7mm)
MR199AX14/C	0.9	5.31 (134.9mm)	3.38 (85.9mm)	3.13 (96.8mm)

