

# Beacons

## Flashing Halogen or Incandescent

### 48 Series

Edwards Signaling 48 Series mid-sized, Halogen and Incandescent flashing beacons are economical, NEMA Type 4X rated devices suitable for use in indoor or outdoor applications where a flashing light source is required. Base material is gray ABS. Unique snap-on, high-impact polycarbonate double fresnel lens is optically engineered to maximize light distribution and viewing distance.

### Features and Specifications

- Halogen or Incandescent light source
- Flash rate 65 fpm
- Quick snap-on, high-impact polycarbonate lens
- Gray ABS base
- Suitable for use in indoor and outdoor applications
- For outdoor use, lens should face up
- Option for panel or conduit mounting
- NEMA Type 4X enclosure
- Operating temperature range: -31°F to 150°F (-35°C to 66°C)



### Ordering Information

Description	Cat. No.	Operating Voltage	Operating Current	Lens Colors	Lamp Ratings <sup>1</sup>	Replacement		
						Lens	Flasher	Lamp
Flashing Beacon Halogen	48FINR-G5-20WH	24V AC	0.80 A	Red	25,000 hr.	96-LR	P-041917-0029	50LMP-20WH or Ind. Trade No. 1692 <sup>2,3</sup>
	48FING-G5-20WH	24V AC	0.80 A	Green	25,000 hr.	96-LG		
	48FINA-G5-20WH	24V AC	0.80 A	Amber	25,000 hr.	96-LA		
	48FINB-G5-20WH	24V AC	0.80 A	Blue	25,000 hr.	96-LB		
	48FINC-G5-20WH	24V AC	0.80 A	Clear	25,000 hr.	96-LC		
	48FINM-G5-20WH	24V AC	0.80 A	Magenta	25,000 hr.	96-LM		
	48FINR-N5-25WH	120V AC	0.20 A	Red	25,000 hr.	96-LR	P-041917-0026	50LMP-25WH or Ind. Trade No. 25T8DC <sup>2,3</sup>
	48FING-N5-25WH	120V AC	0.20 A	Green	25,000 hr.	96-LG		
	48FINA-N5-25WH	120V AC	0.20 A	Amber	25,000 hr.	96-LA		
	48FINB-N5-25WH	120V AC	0.20 A	Blue	25,000 hr.	96-LB		
	48FINC-N5-25WH	120V AC	0.20 A	Clear	25,000 hr.	96-LC		
	48FINM-N5-25WH	120V AC	0.20 A	Magenta	25,000 hr.	96-LM		
	48FINR-G1-20WH	24V DC	0.80 A	Red	25,000 hr.	96-LR	P-041917-0029	50LMP-20WH
	48FING-G1-20WH	24V DC	0.80 A	Green	25,000 hr.	96-LG		
48FINA-G1-20WH	24V DC	0.80 A	Amber	25,000 hr.	96-LA			
48FINB-G1-20WH	24V DC	0.80 A	Blue	25,000 hr.	96-LB			
48FINC-G1-20WH	24V DC	0.80 A	Clear	25,000 hr.	96-LC			
48FINM-G1-20WH	24V DC	0.80 A	Magenta	25,000 hr.	96-LM			
Flashing Beacon Incandescent	48FINR-E1	12V DC	1.0 A	Red	1,520 hr.	96-LR	P-041917-0028	Industry Trade No. 94 <sup>3</sup>
	48FING-E1	12V DC	1.0 A	Green	1,520 hr.	96-LG		
	48FINA-E1	12V DC	1.0 A	Amber	1,520 hr.	96-LA		
	48FINB-E1	12V DC	1.0 A	Blue	1,520 hr.	96-LB		
	48FINC-E1	12V DC	1.0 A	Clear	1,520 hr.	96-LC		
48FINM-E1	12V DC	1.0 A	Magenta	1,520 hr.	96-LM			

<sup>1</sup>Projected lamp life based on manufacturer's calculated lamp life at 65 fpm and 50% duty cycle.

<sup>2</sup>Incandescent lamps

<sup>3</sup>User supplied

