

Beacons

Flashing Halogen

49 Series

Edwards 49 Series flashing Halogen beacons are signaling devices, suitable for use in indoor or outdoor applications where an intermittent (flashing) light source is required. They feature a protective polycarbonate dome and a cast metal base that can be used as a junction box. The double fresnel lens is made of shatter-resistant polycarbonate.

Features and Specifications

- Halogen light source
- Flash rate 65 fpm
- Shatter-resistant double fresnel polycarbonate lens
- Protective polycarbonate dome
- Cast metal base
- Suitable for use in indoor and outdoor applications
- For outdoor use, lens should face up
- 1/2" NPT conduit or surface mounting
- Designed for 4" octagonal box mounting
- Option for panel, conduit or wall mounting
- Operating temperature range: -31°F to 150°F (-35°C to 66°C)



VISUAL SIGNALS 1

Ordering Information

| Description | Cat. No. | Operating Voltage ¹ | Current | Lens Colors | Lamp Ratings | Replacement | | | |
|----------------------------|-------------|--------------------------------|---------|-------------|--|-------------|-------|---------------|---|
| | | | | | | Dome | Lens | Flasher | Lamp |
| Flashing Beacon Halogen | 49R-N5-40WH | 120V AC | 0.30 A | Red | 265 lumens ² 3328 candela | 52-LC | 92-LR | P-041917-0026 | 50LMP-40WH |
| | 49A-N5-40WH | 120V AC | 0.30 A | Amber | | 52-LC | 92-LA | | |
| | 49B-N5-40WH | 120V AC | 0.30 A | Blue | | 52-LC | 92-LB | | |
| | 49G-N5-40WH | 120V AC | 0.30 A | Green | | 52-LC | 92-LG | | |
| | 49M-N5-40WH | 120V AC | 0.30 A | Magenta | | 52-LC | 92-LM | | |
| | 49C-N5-40WH | 120V AC | 0.30 A | Clear | | 52-LC | 92-LC | | |
| | 49R-R5 | 240V AC | 0.10 A | Red | 25 watts 232 lumens ² 2914 candela | 52-LC | 92-LR | P-041917-0038 | P-041917-0039 or Industry Trade No. 25T8/240V/DC/CL ⁴ |
| | 49A-R5 | 240V AC | 0.10 A | Amber | | 52-LC | 92-LA | | |
| | 49B-R5 | 240V AC | 0.10 A | Blue | | 52-LC | 92-LB | | |
| | 49G-R5 | 240V AC | 0.10 A | Green | | 52-LC | 92-LG | | |
| | 49M-R5 | 240V AC | 0.10 A | Magenta | | 52-LC | 92-LM | | |
| | 49C-R5 | 240V AC | 0.10 A | Clear | 52-LC | 92-LC | | | |

¹AC voltage frequency is 50/60 Hz

²Bulb manufacturer's lumen rating

³Projected lamp life based on manufacturer's calculated lamp life at 65 fpm and 50% duty cycle.

⁴User supplied

Accessories

| Description | Cat. No. |
|----------------------|----------|
| Corner Mount Bracket | CBR |
| Wall Mount Bracket | WBR |



CBR
Corner Mount Bracket



WBR
Wall Mount Bracket

