



Custom Work Platforms

Our custom platforms allow you to choose the style, step type, height and configuration to perfectly fit your application. Select a single platform, or choose an extension unit which allows you to add 3' to the width of select platform styles. This unit can be at the same height, or function as a step-down area below existing platforms. Multiple options enable you to build a large surface area that surrounds machinery or spans the entire shop, factory or warehouse floor. 500lb capacity. Rigid 1-1/4" diameter tubing. 36" wide steps. Steps are 7" deep with a deeper 36" platform at top. Grip Strut tread for slip-resistant footing. Meets OSHA standards.



CW0-27-0-3 w/ CW7-27-3-3
Style 7 and Style 0



CW0-27-0-3
Style 0



CW1-27-3-3
Style 1



CW2-27-3-3
Style 2



CW3-27-3-3
Style 3



CW4-27-3-3
Style 4



CW5-27-3-3
Style 5



CW6-27-3-3
Style 6



CW7-27-3-3
Style 7



CW8-27-3-3
Style 8



CW9-27-3-3
Style 9