



Steel Step Stools

Platform Is 16" W x 14" D. 350lb capacity. Rigid 1" square tubing. Perforated or Solid tread covered with nonslip adhesive rubber for slip-resistant footing. Meets OSHA standards.

Shipping Info

Starting Zip
28115

Top Step WxD	Overall WxD	Step Height	Weight	EZY-Tread		Anti-slip Vinyl		Lead Times Days
				EGA #		EGA #		
16x14	18.5x16.5	10 1/2"	16	PSS		RSS		5

Office Ladders



Built with 100% square tube framework for a clean look, Office Ladders come in four standard colors to match your office decor. 450lb capacity. Rigid 1" square tubing. Spring-loaded 3" casters provide mobility while rubber-tipped legs add traction

while in use. 16" and 24" wide steps available. Steps are 7" deep with a deeper 14" top step. Solid treads coated with anti-slip vinyl. Meets OSHA standards. Available colors: blue, gray, black, beige.



Shipping Info

Starting Zip
53005

# Of Steps	Top Step Height	Step Width	Hand Rails	Overall W x L x H	Wt. Lbs.	Anti-Slip Vinyl		Lead Times Days
						EGA #	BL=Black A=Almond B=Blue G=Gray	
1	10	16	N	22x20x10	21	F001		5
2	20	16	N	22x23x20	29	F002		5
2	20	16	Y	22x23x44	37	F003		5
3	30	16	N	22x27x30	37	F004		5
3	30	16	Y	22x29x54	45	F005		5
4	40	16	N	22x35x40	51	F006		5
4	40	16	Y	22x36x64	61	F007		5
5	50	16	Y	23x50x80	77	F008		5
6	60	24	Y	32x57x90	82	F009		5