



## Pumps & Accessories for EBH & EWCH-Cutters

EBH-Series Bar Cutters and EWCH-Series Wire and Cable Cutters are powered by an external pump with an electric valve.

A twin hydraulic hose and electric cable connect the tools to the pump, allowing the user to operate them directly from a control panel located on the cutters.



### ZE4-Series Pumps

Specialized **ZE4-Series** pumps provide a balance of speed and versatility, and are available in 115 and 230 volts. Recommended for use with **EBH30** and **EBH35** cutters when portability, or the convenience of using standard voltage is required.



### ZE6-Series Pumps

Specialized **ZE6-Series** 3-phase pumps offer a high-flow rate that provides fast performance for demanding applications. Recommended for **EBH52** and all **EWCH** cutting applications where speed is critical, or where higher flow rates are required by the application.

## ZE Series



Reservoir Capacity:

**4,6 - 9,8 litres**

Motor Size:

**1,1 - 5,6 kW**

Maximum Operating Pressure:

**700 bar**



### Optional Gauge Kit GKHC

Optional gauge and accessories can be used to monitor pressure in the hydraulic system. Enerpac recommends **GKHC Gauge Kit** for use with Enerpac hydraulic cutters.



### Hoses

EBH-and EWCH-Series Cutters require a twin hose with an electric cable. The hose comes equipped with the appropriate couplers.

Required hoses sold separately.

Description	Model Number
6,1 m long, twin hose with couplers, sheath & electric cable	<b>CH720EC</b>

### Pump Voltage 1-phase: (Model Number ending with suffix)

**B** = 120V, 60 Hz (with American-style NEMA 5-15 plug)

**E** = 230V, 50 Hz (with European-style SCHUKO plug)

**I** = 230V, 50 Hz (with NEMA 6-15 plug)

Pump Series	Pump Model Number *	Motor Electrical Specifications (Volt - Phase, 50-60 Hz)	Motor Size (kW)	Reservoir Capacity (litres)	Dimensions (mm)			Weight (kg)	Required Twin Hose Model Number (Sold separately)	Compatible Cutter Model Number (Sold Separately)
					Height	Length	Width			
ZE4	<b>ZE4404XB</b>	115 V - 1 ph	1,1	4,6	513	521	279	45	<b>CH720EC</b>	<b>EBH30 EBH35</b>
	<b>ZE4404XE</b>	208-240 V - 1 ph								
	<b>ZE4404XI</b>	208-240 V - 1 ph								
ZE6 <sup>1)</sup>	<b>ZE6410XG-S</b>	208-240 V - 3 ph	5,6	9,8	384	559	384	77	<b>CH720EC</b>	<b>All EBH and EWCH-Series Cutters</b>
	<b>ZE6410XJ-S</b>	460-480 V - 3 ph								
	<b>ZE6410XK-S</b>	440 V - 3 ph								
	<b>ZE6410XW-S</b>	380-415V - 3 ph								

\* Indicated pumps come equipped with appropriate configurations to work with indicated cutters.

<sup>1)</sup> ZE6 pumps are available with roll cages. To add a roll cage, add an "R" prior to the "S" in the model number: example **ZE6410XG-RS**.