



STEEL DOLLIES

Capacity to 2,000 lbs.

FEATURES

- ☑ Tough, heavy-duty steel, open frame design
- ☑ Solid platform dollies formed from 11-gauge steel
- ☑ "LU" & "LD" feature 1" lips on all sides
- ☑ All models have towing eye
- ☑ Optional solid steel rod handle

Find our new
Lip-Up/Lip-Down dollies
with bolt-on casters in
The Fairbanks Company's
Value Line catalog

"AI" heavy-duty, open frame dolly has 2" x 1-1/2" x 1/8" welded angle iron, flush top frame. Built to withstand tough factory, warehouse and loading dock requirements. Handles extra heavy loads up to 2000 lbs.*



AI-1830-4HR

Angle iron open frame dolly

Lip-Up and Lip-Down solid platform dollies are formed from a single 11-gauge steel sheet and have 1" lips on all sides. Lip-Up (LU) dollies are ideal for retaining heavy loads. Select Lip-Down (LD) models when a flush, solid steel deck is preferred. All dollies are equipped with four double ball race, swivel casters welded to the frame.

Select either 4" x 1-1/2" hard rubber (HR) wheels, with self-lube bearing, or semi-steel (IW) wheels. Both types of wheels allow for great maneuverability in confined areas and narrow aisles. Durable green epoxy finish.

All steel dollies are shipped knocked down and boxed.

*Rating based on evenly distributed loads



H-37
Towing Handle

For easy movement with heavy loads, all dolly models have a towing eye. The H-37 towing handle is ordered separately. The 3/8" diameter steel rod handle is 37" long.



LU-1830-4HR
Lip-up dolly



LD-1830-4HR
Lip-down dolly

Angle Iron Dollies (AI)				
Deck Size	Part No.	Deck Height	Load Capacity*	Ship Weight
16 x 27	AI-1627-4HR	5-1/2	1600	29
	AI-1627-4IW		2000	32
18 x 30	AI-1830-4HR		1600	30
	AI-1830-4IW		2000	33
24 x 36	AI-2436-4HR		1600	32
	AI-2436-4IW		2000	35

Manufacturer's Note: Dollies shipped knocked down and boxed

* Rating based on evenly distributed loads

Lip-Up Dollies (LU)				
Deck Size	Part No.	Deck Height	Load Capacity*	Ship Weight
16 x 27	LU-1627-4HR	5-3/8	1600	33
	LU-1627-4IW		2000	36
18 x 30	LU-1830-4HR		1600	37
	LU-1830-4IW		2000	40
24 x 36	LU-2436-4HR		1600	55
	LU-2436-4IW		2000	58

Manufacturer's Note: Dollies shipped knocked down and boxed

* Rating based on evenly distributed loads

Lip-Down Dollies (LD)				
Deck Size	Part No.	Deck Height	Load Capacity*	Ship Weight
16 x 27	LD-1627-4HR	5-3/8	1600	33
	LD-1627-4IW		2000	36
18 x 30	LD-1830-4HR		1600	37
	LD-1830-4IW		2000	40
24 x 36	LD-2436-4HR		1600	55
	LD-2436-4IW		2000	58

Manufacturer's Note: Dollies shipped knocked down and boxed

* Rating based on evenly distributed loads