

# LEVER DOLLIES



## C SERIES OAK

Capacity to 5,000 lbs.



Fairbanks' C Series lever dollies feature kiln-dried, 1-3/4" thick, oak handles with rounded edges. Reversed beveled nose iron is 6" wide x 3" deep and bolted to the handle and heavy-duty axle. Handle lengths are 60", 72" and 84". Wheel options are: Semi-steel with plain bore (IW), solid hard rubber with Delrin bearings (HRI), polyurethane mold-on cast on and rubber mold-on cast iron (RT). Lever dollies typically used in pairs.

### C Series Oak

Handle Length	Part No.	Load Capacity	Ship Weight	Wheel Order No.
60	C-60-IW	3500	30	124-A
	C-60-RT	3500	28	525-RC
	C-60-PO	3500	28	825-RC
	C-60-HRI	1000	27	2-315-CC
72	C-72-IW	4250	33	124-A
	C-72-RT	4250	31	525-RC
	C-72-PO	4250	31	825-RC
	C-72-HRI	1000	30	2-315-CC
84	C-84-IW	5000	35	124-A
	C-84-RT	5000	33	525-RC
	C-84-PO	5000	33	825-RC
	C-84-HRI	1000	32	2-315-CC



## E SERIES OAK HARDWOOD

Capacity to 5,000 lbs.



These husky, durable E Series lever dollies easily get under extremely heavy loads with the reversed beveled nose iron, which is bolted to the handle for greater strength. E Series lever dollies have a 5" wide x 3" deep nose iron and the oak hardwood handles have smooth, rounded edges. Wheel options are: Semi-steel with plain bore (IW), polyurethane mold-on cast iron (PO), and rubber mold-on cast iron (RT). Lever dollies typically used in pairs.

### E Series Hardwood

Handle Length	Part No.	Load Capacity	Ship Weight	Wheel Order No.
60	E-60-IW	3500	29	124-A
	E-60-PO	3500	27	825-RC
	E-60-RT	3500	26	525-RC
72	E-72-IW	4250	31	124-A
	E-72-PO	4250	29	825-RC
	E-72-RT	4250	28	525-RC
84	E-84-IW	5000	33	124-A
	E-84-PO	5000	31	825-RC
	E-84-RT	5000	30	525-RC

### Lever Dolly Parts

**C/E72 Axle**  
10-3/4" in length  
7/8" in diameter

**C/E72-L Axle**  
11-3/4" in length  
3/4" in diameter

Lever Dolly No.	Handle Order No.	Ship Weight	Nose Iron Order No.	Ship Weight	Axle Order No.	Ship Weight	Axle Order No.	Ship Weight
C60	C60-HDL	12	C72 Nose Iron	12	C72 Axle*	2.9	C72-L Axle**	2.6
C72	C72-HDL	14		12		2.9		2.6
C84	C84-HDL	16		12		2.9		2.6
E60	E60-HDL	10	E72 Nose Iron	8	E72 Axle*	2.6	E72-L Axle**	2.3
E72	E72-HDL	12		8		2.6		2.3
E84	E84-HDL	14		8		2.6		2.3

\* Axle for IW wheels

\*\* Axle for HRI, PO and RT wheels