

FKD 10 Mixed Flow Fan

10" inline duct fan w/metal housing, 120V, 1~

Item #: 40014

Variant: 115V 1~ 60Hz



This mixed-flow series inline duct fan combines the high airflow of axial fans with the high static pressure characteristics of backward curved impellers. This inline fan is an excellent choice for exhaust or supply applications where high static pressures need to be overcome.

- Mixed-flow impeller enabling high static pressure
- Built-in thermal overload protection with automatic reset
- Galvanized steel housing
- Operable in air stream temperatures up to 140°F
- UL, CSA, HVI, and AMCA Air & Sound certified
- Comes with fan brackets for quick & easy installation
- Limited five-year warranty

The housing is manufactured from galvanized steel for corrosion resistance. The fan uses external rotor motors with a mixed flow impeller that reduces the external dimensions of the fans. General application examples include offices & commercial bathrooms, hospitals, beauty salons, veterinary clinics, and residential applications such as kitchen range hood exhausts.

