

CVS275A Inline Multi-Port Fan

Two 5" intake ports, one 6" exhaust ports, 120V, 1~

Item #: 40116

Variant: 120V 1~ 60Hz



This low-profile fan fits best in applications where multiple intake ports are needed—such as multiple bathrooms or a need for multiple pickup points. The multi-port fan is a popular choice for use in areas between floors in multi-family buildings, high-rise office complexes, or large residential home bathrooms.

- Centrally located exhaust fan with multiple intake ports
- 220 cfm of exhaust air at .2" Pst from two exhaust locations
- Built-in thermal overload protection with automatic reset
- Two 5" intake ports / one 6" exhaust port
- HVI and CSAus Certified
- Five-year factory warranty

Two intake ports connect into one centrally located fan without the use of adapters or transitions. With multiple intake ducts going into one fan, wall or roof penetrations are kept to a minimum. This fan uses a motorized impeller as one integral unit for vibration free, quiet performance.

