

## CVS300A Inline Multi-Port Fan

Four 4" intake ports, one 6" exhaust ports, 120V, 1~

Item #: 40118

Variant: 120V 1~ 60Hz



This low-profile fan fits best in applications where multiple intake ports are needed—such as multiple bathrooms or a need for multiple pickup points. The multi-port fan is a popular choice for use in areas between floors in multi-family buildings, high-rise office complexes, or large residential home bathrooms.

- Designed for home spas or large bathrooms
- Centrally located exhaust fan with multiple intake ports
- 320 cfm of exhaust air at 0.2" Pst from four exhaust locations
- Built-in thermal overload protection with automatic reset
- Four 4" intake ports / One 6" exhaust port
- HVI and CSAus Certified
- Five-year factory warranty

Four intake points connect into one centrally located fan without the use of adapters or transitions. With multiple intake ducts going into one fan, wall or roof penetrations are kept to a minimum. This fan uses a motorized impeller as one integral unit for vibration free, quiet performance.

